



LED EX work light with battery, Type: 3AALH



Order data

Order number	081491 3AALH
GTIN	032705104035
Item class	08C

Description

Version:

Explosion-proof work lamp, tested to the applicable ATEX guideline.

Extremely bright illumination and very long working life.

Multi-functional work lamp with removable magnetic base, sticks to metallic surfaces. Lamp head can be rotated 360° and tilted 120° upwards and downwards (can be locked in any position). With steel clip and front switch.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Bulb	LED module
Tool properties	Suitable for EX areas
Illumination	228 lm
Overall width	54 mm
IP Index of Protection	IP 67

Weight	185 g
ATEX zone	Zone 0
ATEX zone	Zone 20
Number of batteries contained	3
Battery type	Mignon, AA
Overall length	182 mm
Illumination time	8.4 h
Power supply	Battery-powered
Type of product	Flashlight

Accessories

Lithium-metal batteries International size LR6	081559 LR6
Alkaline-manganese batteries International size LR6	081561 LR6
Alkaline-manganese batteries International size LR6	081553 LR6
Alkaline-manganese batteries International size LR6	081554 LR6
Alkaline-manganese batteries International size LR6	081552 LR6
Alkaline-manganese batteries International size LR6	081551 LR6