



Open ended spanner / ratchet ring spanner reversible 15° offset, Width across flats: 11 mm



Order data

Order number	614905 11
GTIN	3662424064999
Item class	63V

Description

Version:

Drop-forged. Ring and fork with ratchet effect. The additional ratchet mechanism at the open jaws permits quick tightening without having to re-apply the wrench. The ring end has an integral spring to prevent it slipping over the fastener being tightened – reversible for left- and right-hand tightening. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, chrome-plated.

Technical description

Jaw width b	23.7 mm
Width across flats	11 mm
Jaw height h ₁	5.2 mm
Ring Ø D	22 mm
Ring thickness h ₂	7.7 mm
Spanner length L	165 mm
Width across flats	metric
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome-plated

with swivel head	no
Ratchet reversible	yes
Type of product	Spanner