

Garant
Through hole machine tap, uncoated, MF: M46X3

Order data

Order number	130000 M46X3
GTIN	4062406278878
Item class	10N

Description
Note:

Delivery time: 35 calendar days

Minimum order quantity: 1 pc.

Special / custom-made product - return not possible

Thread type: M

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 1 4H

Tolerance class: ISO 1X 4HX

Tolerance class: ISO 2 6H

Thread pitch: 3 mm

Overall length L: 250 mm

Shank $\varnothing D_s$: 36 mm

Shank square \square : 29 mm

Tapping hole \varnothing : 43 mm

Technical description

Number of clamping slots	4
Tapping hole \varnothing	43 mm
Shank $\varnothing D_s$	36 mm
Standard	DIN 376
Tolerance class	ISO 1 4H
Tolerance class	ISO 1X 4HX

Tolerance class	ISO 2 6H
Tolerance class	ISO 2X 6HX
Tolerance class	6H +0.05
Tolerance class	ISO 3 6G
Tolerance class	ISO 3X 6GX
Tolerance class	7H
Tolerance class	7HX
Tolerance class	7G
Tolerance class	7GX
Tolerance class	6H +0.10
Tolerance class	6H +0.20
Overall length L	250 mm
Thread \varnothing	46 mm
Shank square \square	29 mm
Thread pitch	3 mm
Thread size	M46x3
Thread depth	138 mm
Thread type	M
Tool material	HSS E
Number of cutting edges Z	4
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3xD for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining

Colour ring	without
Type of product	Tap