

Garant
GARANT Master Alu solid carbide high-performance reamer HPC through hole, DLC, Nominal Ø DC: 15mm

Order data

Order number	164400 15
GTIN	4062406283810
Item class	10P

Description
Version:

Special HPC reamers of the latest generation, **for machining aluminium**, with improved tooth geometry and further developed carbide substrate. Extra-short teeth for increased cutting performance values. Optimised cooling strategy with radially arranged coolant outlets aligned directly to the teeth. **Version suitable for NC** with straight shank Ø for standard arbors especially in **hydraulic chucks** or **high precision collet chucks**. Very high concentricity and process reliability due to unequal spacing of the teeth and special profile of the round chamfer width.

Version with DLC sp² coating.

Tolerance specifications:

Configurable: Reamers finish ground to match your specification.

H7: Version to DIN1420 for H7 bore tolerance.

Application:

Special version for through holes.

Technical description

Shank Ø D _s	16 mm
Ø range	14.201 - 15.2 mm
Number of cutting edges Z	6
Overall length L	130 mm
Overhang L ₁	82 mm
Tolerance	configurable

Series	Master Alu
Flute length L_c	15 mm
Feed f in cast alu	2.1 mm/rev.
Nominal $\varnothing D_c$	15 mm
Reaming oversize in diameter	0.2 mm
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA with h6
Machining strategy	HPC
Application for type of drilling	for through holes
Colour ring	yellow
Type of product	Phillips bit

User data

	Suitability	V_c	ISO code
Aluminium	suitable	250 m/min	N
Aluminium (short chipping)	suitable	250 m/min	N
Alu > 10% Si	suitable	250 m/min	N
wet maximum	suitable		
wet minimum	suitable		