

3M**VHB™ adhesive tape, black, Width×length (mm× m): 25X33**

Order data

Order number	083782 25X33
GTIN	4001895877339
Item class	08M

Description

Version:

Double-sided high-performance **adhesive tape** of pure acrylate adhesive (VHB) for permanently strong bonds. High instant tack, high resistance to temperature, weather, UV and solvents. Excellent sealing function, vibration-damping.

The **3M™ 5952** means reliability right across the board. It offers optimum adaptability to the surfaces to be bonded. This feature permits even thin and structured surfaces to be joined without any sort of stress.

Note:

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Further 3M™ VHB™ tapes in different thicknesses and lengths are available on request.

Adhesive: Acrylate

Length: 33 m

Width: 19 mm

Thickness: 1.6 mm

Technical description

"Best before" date	12 mo
Adhesive strength on steel	5.5 N/mm
Width	19 mm
Adhesive	Acrylate
Special features	clings well
Special features	damping
Special features	moisture-resistant
Thickness	1.6 mm
Manufacturer's designation	5962F
Length	33 m
Type of adhesive tape	double-sided
Stretch capability	300 %
temperature-resistant up to	120 - 150 °C
Colour	grey
Application	Attaching
Application	Sealing
Application	Masking
Application	Assembly
Storage temperature	20 °C
Material of covering	Paper
Storage humidity	50 %
Product name attribute	black
Type of product	Adhesive tape