

**Garant**
**GARANT Master Alu solid carbide slot drill DIN 6535 HA, DLC, Ø DC: 10mm**

**Order data**

Order number	201260 10
GTIN	4062406281205
Item class	11X

**Description**
**Version:**

Stronger cutting edges.

Dimensions similar to DIN 6527.

With the latest generation of **DLC coating sp<sup>2</sup>**.

**Advantage:**

Very smooth cutting action for **outstanding surface quality**.

**Technical description**

Shank	DIN 6535 HA to h6
Overall length L	72 mm
Overhang length L <sub>1</sub> incl. recess	29 mm
Corner chamfer angle	90 degrees
Balance quality with shank	G 2.5 with HA
No. of teeth Z	2
Feed f <sub>z</sub> for slot milling in short-chipping aluminium	0.09 mm
Direction of infeed	horizontal, oblique and vertical
Cutting edge Ø D <sub>c</sub>	10 mm
Tolerance nominal Ø	e6
Recess Ø D <sub>1</sub>	9.7 mm
Flute length L <sub>c</sub>	22 mm

Shank $\varnothing D_s$	10 mm
Feed $f_z$ for side milling in short-chipping aluminium	0.12 mm
Helix angle	38 degrees
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	DIN 6527
Type	W
Cutting width $a_e$ for milling operation	0.5×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	yellow
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Aluminium	Suitable	550 m/min	N
Aluminium (short chipping)	suitable	500 m/min	N
Alu > 10% Si	suitable	450 m/min	N
PMMA acrylic	Suitable	200 m/min	N
PE-HD	Suitable	160 m/min	N
PA 66	Suitable	200 m/min	N
PEEK	Suitable	150 m/min	N
PF 31	Suitable	130 m/min	N
PVDF GF20	suitable	180 m/min	N
POM GF25	suitable	160 m/min	N
PA 66 GF30	suitable	150 m/min	N
PEEK GF30	suitable	130 m/min	N

PTFE CF25	suitable	160 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	300 m/min	N
Cu	Suitable	160 m/min	N
CuZn	Suitable	200 m/min	N
wet maximum	suitable		
wet minimum	suitable		
dry	suitable only under restricted conditions		
Air	suitable		