

**Garant****GARANT Master Alu solid carbide high-performance reamer HPC blind hole, DLC, Nominal Ø DC: 10H7mm****Order data**

Order number	164405 10H7
GTIN	4062406282165
Item class	10P

**Description****Version:**

**Special** HPC reamers of the latest generation, **for machining aluminium**, with improved tooth geometry and further developed carbide substrate. Extra-short teeth for increased cutting performance values. Optimised cooling strategy with radially arranged coolant outlets aligned directly to the teeth. **Version suitable for NC** with straight shank Ø for standard arbors especially in **hydraulic chucks** or **high precision collet chucks**. Very high concentricity and process reliability due to unequal spacing of the teeth and special profile of the round chamfer width.

Version with DLC sp<sup>2</sup> coating.

**Tolerance specifications:**

**Configurable:** Reamers finish ground to match your specification.

**H7:** Version to DIN1420 for H7 bore tolerance.

**Application:**

Special version for blind holes.

**Technical description**

Number of cutting edges Z	6
Overall length L	120 mm
Tolerance	H7
Nominal Ø D <sub>c</sub>	10 mm
Flute length L <sub>c</sub>	12 mm
Series	Master Alu

Shank Ø D <sub>s</sub>	10 mm
Feed f in cast alu	1.8 mm/rev.
Overhang L <sub>1</sub>	80 mm
Reaming oversize in diameter	0.1 mm
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA with h6
Machining strategy	HPC
Application for type of drilling	for blind holes
Colour ring	yellow
Type of product	Phillips bit

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium	suitable	250 m/min	N
Aluminium (short chipping)	suitable	250 m/min	N
Alu > 10% Si	suitable	250 m/min	N
wet maximum	suitable		
wet minimum	suitable		