



## Open ended spanner / ratchet ring spanner reversible 15° offset, Width across flats: 14mm



### Order data

Order number	614905 14
GTIN	3662424065026
Item class	63V

### Description

#### Version:

Drop-forged. Ring and fork with ratchet effect. The additional ratchet mechanism at the open jaws permits quick tightening without having to re-apply the wrench. The ring end has an integral spring to prevent it slipping over the fastener being tightened – reversible for left- and right-hand tightening. Extremely small working arc of 5°.

#### Material:

Chrome vanadium steel, chrome-plated.

### Technical description

Width across flats	14 mm
Jaw width b	30.8 mm
Ring Ø D	27 mm
Jaw height h <sub>1</sub>	5.9 mm
Ring thickness h <sub>2</sub>	9 mm
Width across flats	metric
Spanner length L	190 mm
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome-plated

with swivel head	no
Ratchet reversible	yes
Type of product	Spanner