



## Open ended spanner / ratchet ring spanner reversible 15° offset, Width across flats: 19mm



### Order data

Order number	614905 19
GTIN	3662424065071
Item class	63V

### Description

#### Version:

Drop-forged. Ring and fork with ratchet effect. The additional ratchet mechanism at the open jaws permits quick tightening without having to re-apply the wrench. The ring end has an integral spring to prevent it slipping over the fastener being tightened – reversible for left- and right-hand tightening. Extremely small working arc of 5°.

#### Material:

Chrome vanadium steel, chrome-plated.

### Technical description

Ring thickness $h_2$	11.2 mm
Width across flats	19 mm
Jaw width $b$	41.2 mm
Jaw height $h_1$	7.4 mm
Spanner length $L$	247 mm
Ring $\varnothing D$	33.9 mm
Width across flats	metric
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome-plated

with swivel head	no
Ratchet reversible	yes
Type of product	Spanner