

**Garant**
**GARANT Master Steel solid carbide ball nose slot drill HPC, TiAlN, Ø f8 DC / D S: 8mm**

**Order data**

Order number	207244 8
GTIN	4062406285203
Item class	11X

**Description**
**Version:**

**Precision ground for very high accuracy requirements.**

Tolerance: Radius contour =  $\pm 0.005$  mm.

Improved cutting edge protection thanks to slight edge honing. Tremendous bending strength due to the use of ultra-fine grain substrate.

**Technical description**

Cutting edge $\varnothing D_c$	8 mm
Feed $f_z$ for copy milling in steel < 900 N/mm <sup>2</sup>	0.12 mm
Helix angle	28 degrees
Shank $\varnothing D_s$	8 mm
Flute length $L_c$	12 mm
Overall length L	100 mm
No. of teeth Z	2
Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.1 mm
Radius R	4 mm
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide

Standard	Manufacturer's standard
Type	N
Tolerance nominal $\varnothing$	f8
Direction of infeed	horizontal, oblique and vertical
Cutting width $a_e$ for milling operation	0.5×D for side milling
Cutting width $a_e$ for milling operation	0.03×D for copy milling
Shank	DIN 6535 HA to h6
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	Ball-nosed slot drill

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	Suitable	260 m/min	P
Steel < 750 N/mm <sup>2</sup>	Suitable	230 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	210 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	160 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	130 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	85 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	75 m/min	M
GG(G)	suitable only under restricted conditions	350 m/min	K
Uni	Suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

dry	Suitable
Air	Suitable