

## Garant

### GARANT Master Alu solid carbide high-performance reamer HPC through hole, DLC, Nominal Ø DC: 6,5mm



#### Order data

Order number	164400 6,5
GTIN	4062406283674
Item class	10P

#### Description

##### Version:

**Special** HPC reamers of the latest generation, **for machining aluminium**, with improved tooth geometry and further developed carbide substrate. Extra-short teeth for increased cutting performance values. Optimised cooling strategy with radially arranged coolant outlets aligned directly to the teeth. **Version suitable for NC** with straight shank Ø for standard arbors especially in **hydraulic chucks** or **high precision collet chucks**. Very high concentricity and process reliability due to unequal spacing of the teeth and special profile of the round chamfer width.

Version with DLC sp<sup>2</sup> coating.

##### Tolerance specifications:

**Configurable:** Reamers finish ground to match your specification.

**H7:** Version to DIN1420 for H7 bore tolerance.

##### Application:

Special version for through holes.

#### Technical description

Overall length L	100 mm
Flute length L <sub>c</sub>	10 mm
Nominal Ø D <sub>c</sub>	6.5 mm
Feed f in cast alu	1 mm/rev.
Tolerance	configurable
Number of cutting edges Z	6

Shank $\varnothing D_s$	8 mm
Overhang $L_1$	64 mm
Series	Master Alu
$\varnothing$ range	6.201 - 6.7 mm
Reaming oversize in diameter	0.1 mm
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA with h6
Machining strategy	HPC
Application for type of drilling	for through holes
Colour ring	yellow
Type of product	Phillips bit

## User data

	Suitability	$V_c$	ISO code
Aluminium	suitable	250 m/min	N
Aluminium (short chipping)	suitable	250 m/min	N
Alu > 10% Si	suitable	250 m/min	N
wet maximum	suitable		
wet minimum	suitable		