

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 10/07mm

Order data

Order number	261333 10/07
GTIN	4062406283599
Item class	21T

Technical description

Setting angle κ	95 degrees
Insert size	7 mm
Pack of insert screws	269028 26
Clamping height L_2	9 mm
ISO code toolholder	E10H SVLCR/L07
Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
suitable indexable insert	VC.. 0702..
Overall length L	100 mm
Centre offset L_3	7 mm
Neck width L_4	7.5 mm
Usable depth T	5 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------