

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 12/07mm

Order data

Order number	261342 12/07
GTIN	4062406285623
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
suitable indexable insert	VC.. 0702..
Pack of insert screws	269028 26
ISO code toolholder	E12K SV95CR/L07
Neck width L_4	9 mm
Clamping height L_2	11 mm
Overall length L	125 mm
Head length L_1	40 mm
Insert size	7 mm
Setting angle κ	95 degrees
Centre offset L_3	9 mm
Usable depth T	6 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------