

**Garant**
**Arbor for screw-in milling cutters with thread, SK 30, Thread M × Length L1: M12X25**

**Order data**

Order number	301316 M12X25
GTIN	4062406286064
Item class	31A

**Description**
**Version:**

Tapered design.

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Machining strategy: HSC

Overhang dimension A: 44 mm

Bore  $\varnothing D_1$  tolerance IT6: 12.5 mm

$\varnothing D_2$ : 21 mm

External  $\varnothing D$ : 24 mm

Reach  $L_1$ : 25 mm

$L_2$ : 5 mm

**Technical description**

$L_2$	5 mm
$\varnothing D_2$	21 mm
Reach $L_1$	25 mm
Overhang dimension A	44 mm

Thread M	M12×25
Bore Ø D <sub>1</sub> tolerance IT6	12.5 mm
External Ø D	24 mm
Adapter	SK 30
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Type of product	Threaded copy mill arbor