

Garant
**Arbor for screw-in milling cutters with thread, SK 30, Thread M × Length L1:
M8X25**

Order data

Order number	301316 M8X25
GTIN	4062406286040
Item class	31A

Description
Version:

Tapered design.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Machining strategy: HSC

Overhang dimension A: 44 mm

Bore $\varnothing D_1$ tolerance IT6: 8.5 mm

$\varnothing D_2$: 13 mm

External $\varnothing D$: 15 mm

Reach L_1 : 25 mm

L_2 : 5 mm

Technical description

Thread M	M8x25
$\varnothing D_2$	13 mm
Overhang dimension A	44 mm
L_2	5 mm

Bore $\varnothing D_1$ tolerance IT6	8.5 mm
Reach L_1	25 mm
External $\varnothing D$	15 mm
Adapter	SK 30
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Threaded copy mill arbor