

Garant
**Arbor for screw-in milling cutters with thread, SK 30, Thread M × Length L1:
M10X25**

Order data

Order number	301316 M10X25
GTIN	4062406286057
Item class	31A

Description
Version:

Tapered design.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Machining strategy: HSC

Overhang dimension A: 44 mm

Bore $\varnothing D_1$ tolerance IT6: 10.5 mm

$\varnothing D_2$: 18 mm

External $\varnothing D$: 20 mm

Reach L_1 : 25 mm

L_2 : 5 mm

Technical description

Thread M	M10×25
External $\varnothing D$	20 mm
Bore $\varnothing D_1$ tolerance IT6	10.5 mm
Overhang dimension A	44 mm

Reach L ₁	25 mm
L ₂	5 mm
Ø D ₂	18 mm
Adapter	SK 30
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Type of product	Threaded copy mill arbor