

**LESSMANN®**  
THE GERMAN BRUSH COMPANY**Single-row wheel brush micro-abrasive 0.6 mm, SiC 120, Brush Ø D1× brush width: 250X16mm****Order data**

Order number	570320 250X16
GTIN	4017359163863
Item class	57L

**Description****Version:**

**Single-row brush** with waved brush material.

**Application:**

For roughening, cleaning, removing rust, and scale etc. Single-row brushes can be mounted alongside each other **to form various effective brushing widths**. For individual use on grinding machines.

**Technical description**

Brush Ø D <sub>1</sub>	250 mm
maximum speed	6000 min <sup>-1</sup>
Bore Ø can be opened up to	100 mm
Brush width	16 mm
Length of brush section H <sub>1</sub>	57 mm
Bore Ø d <sub>1</sub>	16 mm

Grinding media	Silicon carbide (SiC) grit
Brush material	micro-abrasive, abrasive nylon
Grinding medium code	SiC
Bristle thickness	0.6 mm
Type of product	Wheel brush