

LESSMANN®
THE GERMAN BRUSH COMPANY**End brush Stainless steel complete 0.30 mm, Type: 22X22****Order data**

Order number	574650 22X22
GTIN	4017359098158
Item class	57L

Description**Version:**

Waved special high quality wire, crimped into steel ferrule, **shank Ø 6 mm**.
All components of stainless steel.

Application:

For straight die grinders, on flexible drive machines and drills. For cleaning and deburring at inaccessible places.

Technical description

Clamp Ø D ₂	22 mm
Length of brush section H ₁	25 mm
maximum speed	18000 min ⁻¹
Brush Ø D ₁	23 mm
Clamp length L ₂	22 mm
Bristle thickness	0.3 mm
Overall length L	68 mm
Shank Ø D _s	6 mm
Type of product	End brush

