




Platform trolley with tubular struts on 3 sides and 4 loading platforms, Type: 8312-1



Order data

Order number	919881 8312-1
GTIN	4017976831213
Item class	96F

Description

Version:

Welded steel sections and tubes, end walls with vertical tube struts at 130 mm spacing. One long wall with tubular struts for insertion. Platforms made of chipboard with beech grain surface. Intermediate shelves adjustable at 100 mm intervals. The bottom shelf is not adjustable. 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Wheel Ø	200 mm
Depth	730 mm

Load capacity of each loose shelf	90 kg
Height of shelf 1	269 mm
Platform area width	1000 mm
Width	1169 mm
Height of shelf 2	669 mm
Height of shelf 3	1069 mm
Total load capacity	600 kg
Height of shelf 4	1469 mm
Height	1800 mm
Platform area depth	700 mm
Weight	95 kg
Height adjustment interval	100 mm
Type of product	Platform trolley