

**Enclosed trolley with sheet metal walls, with 5 loading platforms, Type: 5493****Order data**

Order number	919883 5493
GTIN	4017976019192
Item class	96F

**Description****Version:**

Steel angle section construction with tubular pushing handle. End walls, long wall, swing door and roof clad with 1 mm thick galvanised sheet metal. Double swing door of steel angle section with positive bar locking with pivoting handle and padlock. 1 fixed platform and 4 loose shelves of chipboard with beech grain surface. Intermediate shelves adjustable at 100 mm intervals. The bottom shelf is not adjustable. 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings. TOTALSTOP central braking system on the castors.

**Standard:****EN 1757-3****Colour:**Brilliant blue RAL 5007 **powder-coated.****Technical description**

Platform area depth	780 mm
Height of shelf 1	292 mm
Height of shelf 2	582 mm

Depth	845 mm
Wheel Ø	200 mm
Height of shelf 4	1182 mm
Total load capacity	750 kg
Width	1370 mm
Height of shelf 3	882 mm
Height of shelf 5	1482 mm
Weight	199 kg
Load capacity of each loose shelf	90 kg
Platform area width	1200 mm
Material of wheel	TPE
Height	1792 mm
Height adjustment interval	100
Type of product	Enclosed trolley