

**Enclosed trolley with sheet metal walls, with 5 loading platforms, Type: 5492****Order data**

| | |
|--------------|---------------|
| Order number | 919883 5492 |
| GTIN | 4017976019185 |
| Item class | 96F |

Description**Version:**

Steel angle section construction with tubular pushing handle. End walls, long wall, swing door and roof clad with 1 mm thick galvanised sheet metal. Double swing door of steel angle section with positive bar locking with pivoting handle and padlock. 1 fixed platform and 4 loose shelves of chipboard with beech grain surface. Intermediate shelves adjustable at 100 mm intervals. The bottom shelf is not adjustable. 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings. TOTALSTOP central braking system on the castors.

Standard:**EN 1757-3****Colour:**Brilliant blue RAL 5007 **powder-coated.****Technical description**

| | |
|---------------------|---------|
| Height of shelf 3 | 882 mm |
| Total load capacity | 750 kg |
| Height of shelf 5 | 1482 mm |

| | |
|-----------------------------------|------------------|
| Height of shelf 2 | 582 mm |
| Height of shelf 4 | 1182 mm |
| Weight | 162 kg |
| Height of shelf 1 | 292 mm |
| Platform area depth | 680 mm |
| Load capacity of each loose shelf | 90 kg |
| Depth | 745 mm |
| Platform area width | 1000 mm |
| Width | 1170 mm |
| Height | 1792 mm |
| Material of wheel | TPE |
| Wheel Ø | 200 mm |
| Height adjustment interval | 100 |
| Type of product | Enclosed trolley |