

LESSMANN®
THE GERMAN BRUSH COMPANY

Single-row wheel brush micro-abrasive 0.6 mm, SiC 320, Brush Ø×brush width: 250X16mm



Order data

| | |
|--------------|---------------|
| Order number | 570322 250X16 |
| GTIN | 4017359163856 |
| Item class | 57L |

Description

Version:

Single-row brush with waved brush material.

Application:

For roughening, cleaning, removing rust, and scale etc. Single-row brushes can be mounted alongside each other **to form various effective brushing widths**. For individual use on grinding machines.

Technical description

| | |
|--|------------------------|
| Bore Ø can be opened up to | 100 mm |
| maximum speed | 6000 min ⁻¹ |
| Length of brush section H ₁ | 57 mm |
| Brush width | 16 mm |
| Brush Ø D ₁ | 250 mm |
| Bore Ø d ₁ | 16 mm |

| | |
|----------------------|--------------------------------|
| Grinding media | Silicon carbide (SiC) grit |
| Brush material | micro-abrasive, abrasive nylon |
| Grinding medium code | SiC |
| Bristle thickness | 0.6 mm |
| Type of product | Wheel brush |