

Garant**Mesh trolley TG9 with 5 loading platforms, Type: TG96****Order data**

| | |
|--------------|---------------|
| Order number | 918565 TG96 |
| GTIN | 4062406295639 |
| Item class | 9GT |

Description**Version:**

Welded steel construction, shelves of **chipboard** with anthracite-coloured scratch-resistant surface. Adjustable at 40 mm intervals. Fold-away handle at the side with 2-component Haptoprene coating permits a very wide door opening angle. With 2 ball-bearing fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres, Ø 200 mm. Can be centrally locked by 2-component Haptoprene push handle using a cylinder lock.

Standard:**EN 1757-3****Optional extras:**

Additional shelf No. 918578.

Colour:Silver **powder-coated**.**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

| | |
|---------------------|--------|
| Platform area depth | 700 mm |
|---------------------|--------|

| | |
|-----------------------------------|------------------|
| Total load capacity | 500 kg |
| Weight | 136 kg |
| Platform area width | 1000 mm |
| Load capacity of each loose shelf | 85 kg |
| Height | 1835 mm |
| Width | 1200 mm |
| Wheel Ø | 200 mm |
| Depth | 710 mm |
| Door opening angle | 250 degrees |
| Height adjustment interval | 40 |
| Cylinder lock | modular barrel |
| Type of product | Enclosed trolley |

Accessories

| | |
|---|------------|
| Intermediate shelf for slotting into mesh trolley TG9 Platform area depth 700 mm | 918578 700 |
|---|------------|