



Core drilling machine, Type: MAB155



Order data

Order number	076535 MAB155
GTIN	4250187513893
Item class	07E

Description

Version:

- **Integral internal lubrication system, magnetic indicator for monitoring the magnetic clamping force.**
- **Integral cutting oil container, complete cable routing within the casing.**
- **Oil bath gearbox.**

Note:

- **See No. 118780 to 118825 for core drills.**
- **Core drilling machines with automatic feed, vacuum clamping plate and pipe clamping fixtures available on request.**
- **Pneumatic core drilling machines with ATEX standard available on request.**

Packaging: Carrying case

Manufacturer's designation: MAB 155

Power consumption: 1050 W

maximum speed: 320 min⁻¹

maximum core drill Ø in steel: 35 mm

Boring depth: 30 mm

Length of magnetic base: 80 mm

Technical description

Length of magnetic base	80 mm
Boring depth	30 mm

Power consumption	1050 W
Working stroke	39 mm
Width of the magnetic base	160 mm
Manufacturer's designation	MAB 155
Weight	11 kg
maximum speed	320 min ⁻¹
maximum core drill Ø in steel	35 mm
AC supply voltage	230 V
Power supply	Mains operated
Packaging	Carrying case
Type of product	Core drilling machine