



## Pneumatic screwdriver, Type: S2307CE

### Order data

|              |                |
|--------------|----------------|
| Order number | 079163 S2307CE |
| GTIN         | 7322590038373  |
| Item class   | 03R            |

### Description

#### Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø.

- **With slip clutch.**
- **Adjustable torque setting.**
- **Reversible for clockwise/ anticlockwise rotation.**

Particularly suitable for series production screwdriving with quick-release bit holder for E 6.3 bits (see No. 674205 ff). Torque is externally adjustable using a twist sleeve.

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Torque range: 2,5 – 10 N·m

maximum screw Ø (8.8 - 12.9): M6

maximum speed: 900 min<sup>-1</sup>

Tool arbor size: 1/4 in

Format: Pistol

maximum air consumption: 504 l/min

### Technical description

|                            |              |
|----------------------------|--------------|
| Format                     | Pistol       |
| maximum air consumption    | 504 l/min    |
| Torque range               | 2,5 – 10 N·m |
| Weight                     | 1.2 kg       |
| Manufacturer's designation | S2307CE      |
| Tool arbor size            | 1/4 in       |
| Operating noise            | 82 dB(A)     |

## Data sheet

|                                    |                        |
|------------------------------------|------------------------|
| recommended hose size (internal Ø) | 10 mm                  |
| maximum speed                      | 900 min <sup>-1</sup>  |
| maximum vibration to EN            | < 2.5 m/s <sup>2</sup> |
| maximum screw Ø (8.8 - 12.9)       | M6                     |
| Compressed air connection          | 1/4 in                 |
| Connection thread                  | BSP                    |