

**Garant****Fleece velour-backed abrasive disc, Ø 115 mm, Grit equivalent: 100****Order data**

Order number	566911 100
GTIN	4062406297749
Item class	51M

**Description****Version:**

Fleece velour-backed abrasive discs with through-stitched backing for hook and loop fastener. With removable centre for more precise positioning and attachment of the disc to the backing pad (**approx. 50 % reduction in vibration level with velour-backed abrasive discs No. 566965**).

**Application:**

On angle grinders with hook and loop fastener backing pad No. 566960 or 566965.

For **finishing, matting, smoothing** with significant reduction in roughness, and for **light cleaning** (such as removal of discolouration) and **deburring tasks**.

**Note:**

See No. **567705ff** onwards for velour-backed abrasive discs for rough abrasion.

maximum circumferential speed: 40 m/s

Grit designation: coarse

Version: A coarse

Colour: brown

**Technical description**

Grit designation	coarse
Version	A coarse
Disc Ø	115 mm
Colour	brown
Grit equivalent	100
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 115 mm
maximum circumferential speed	40 m/s
Type of product	Non-woven abrasive

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		

dry

suitable

---

**Accessories**

---

Hook and loop backing pad with Thread M 14 External Ø  
115 mm

566960 115

---

Hook and loop backing pad with Centring and M 14 thread  
External Ø 115 mm

566965 115