



GÜNZBURGER STEIGTECHNIK

Mobile machine platform with height adjustment, Number of steps including platform: 1



Order data

Order number	966205 1
GTIN	4031405304147
Item class	98G

Description

Version:

Sturdy aluminium structure with 2-part fold-away feet for three different working heights (2.25 m; 2.5 m; 2.75 m). Non-slip platform of marine plywood, sufficient room for two persons and work equipment, standing area 1.7 × 0.6 m. 65 mm deep, serrated steps for safe ascent and descent. With rollers for easy movement. Non-slip plastic end caps. Maximum load capacity 300 kg. Easy transport with transport dimensions (W × D × H in m): 1.71 × 0.74 × 0.25.

Technical description

Type of step	step
Weight	24.5 kg
Rung/step depth	65 mm
Footprint depth	0.73 m
Platform height without railing	0.25 m
Platform height without railing	0.48 m
Platform height without railing	0.73 m
Footprint width	1.71 m

Footprint width	2 m
Footprint width	2.2 m
Working height approx.	2.25 m
Working height approx.	2.5 m
Working height approx.	2.75 m
Rollers	yes
height-adjustable	yes
Ladders and platforms load capacity	300 kg
Type of product	Work platform