



## Cleaning-Stick, Length L: 70mm



### Order data

Order number	358966 70
GTIN	
Item class	38L

### Description

#### Advantage:

- Thorough cleaning of the interior of the machine.
- Perfect complement to the automated work process.
- Suitable for cooling lubricants (5 – 120 bar) and compressed air (5 – 10 bar).

#### Application:

- Particularly suitable for cleaning out holes, pockets and undercuts.
- Directed approach to the position to be cleaned.
- For installation in any toolholder with through-coolant capability.

#### Optional extras:

Universal nozzles No. 358967.

### Technical description

Shank Ø	16 mm
Speed range	30 - 400 min <sup>-1</sup>
Working medium	Cooling lubricant
Working medium	Compressed air
Type of product	Nozzle

---

## Accessories

Universal nozzles for cleaning stick Type 50	358967 50
Universal nozzles for cleaning stick Type 45	358967 45