



Multi-standard jacket VIS-LINE, yellow / cornflower blue, Clothing size DE: 110



Order data

| | |
|--------------|---------------|
| Order number | 091701 110 |
| GTIN | 4057121456786 |
| Item class | 09S |

Description

Version:

The VIS-LINE multi-standard clothing with the **ergonomic dynamic fit** is very hard-wearing and tear-resistant. With its modern design and wide variety of colours, the clothing **combines very well with the PRO-LINE** from Rofa. The **reflective elements** are applied on the roof tile principle, so they are easily repaired if required.

The jacket has **pre-shaped sleeves** which ensure optimum freedom of movement.

- **Fold-down collar.**
- **Front middle with snap fasteners.**
- **Breast and side pockets with flaps and snap fasteners.**
- **Adjustable sleeves with snap fasteners.**
- **Free-movement pleats in the back part.**
- **Large inside breast pocket with hook and loop fastening.**
- **Extended back.**

Standard:

- EN ISO 20471 Klasse 2
- EN 1149-3/-5
- EN ISO 11612 A1, A2, B1, C1, E3, F1
- EN ISO 11611 Klasse 1/A1+A2
- EN 13034 Typ 6
- EN 61482-1-2

Note:

Available in other colours on request. Size table showing equivalent international sizes can be found on our information section at the end of the catalogue.

Jacket with **EN ISO 20471 class 1** in cornflower blue / yellow under No. 091702.

Technical description

| | |
|----------------------------------|---|
| Gender | Gentlemen's |
| Clothing size DE | 110 |
| Series | VIS-LINE |
| Fabric composition | 65% cotton |
| Fabric composition | 2% other fibres |
| Fabric composition | 33% polyester |
| Material weight / fabric density | 350 g/m ² |
| Washing | 60 °C coloureds |
| Colour | yellow / cornflower blue |
| Standard | EN 13034-6 |
| Standard | EN 61482-1-2 |
| Standard | EN ISO 20471 |
| Clothing to | DIN EN ISO 1149 anti-static characteristics |
| Clothing to | DIN EN ISO 11612 protection against flames and heat |
| Clothing to | DIN EN ISO 11612 protection against flames and heat |
| Type of product | High visibility jacket |