

Garant**Hybrid mechanic's gloves, Glove size: 11****Order data**

Order number	094005 11
GTIN	4062406295523
Item class	01H

Description**Version:**

Robust but very flexible mechanic's gloves for heavy-duty activities and handling heavy, bulky objects. The palm is made from extremely abrasion-resistant synthetic leather. A padded area also absorbs knocks and impacts and therefore additionally protects the hand. The back of the glove is resilient and breathable to ensure the greatest possible comfort. The index fingers of the gloves are compatible with touch screens. This means that the wearer can use devices like a smartphone without needing to take the gloves off.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	11
Protection category	Category II
Type of glove	Multi-purpose gloves

Contents	1
Drying	air dry
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	Hook & loop fastener
Glove characteristics	Suitable for touch screens
Glove characteristics	DMF-free
EN 388	4111X
Backing material	Synthetic leather/Spandex
Application range	Heavy Duty
Length	240 mm
AQL	G-II 1.0 for critical, G-II 2.5 for major, G-II 4.0 for minor.
Application	reusable
Cut protection class	FG
Type of product	Multi-purpose gloves