

**Garant****Mesh trolley TG9 with 5 loading platforms, Type: TG96****Order data**

Order number	918565 TG96
GTIN	4062406295639
Item class	9GT

**Description****Version:**

Welded steel construction, shelves of **chipboard** with anthracite-coloured scratch-resistant surface. Adjustable at 40 mm intervals. Fold-away handle at the side with 2-component Haptoprene® coating permits a very wide door opening angle. With 2 ball-bearing fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres, Ø 200 mm. Can be centrally locked by 2-component Haptoprene® push handle using a cylinder lock.

**Standard:**

**EN 1757-3**

**Optional extras:**

Additional shelf No. 918578.

**Colour:**

Silver **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Platform area depth	700 mm
---------------------	--------

Total load capacity	500 kg
Weight	136 kg
Platform area width	1000 mm
Load capacity of each loose shelf	85 kg
Height	1835 mm
Width	1200 mm
Wheel Ø	200 mm
Depth	710 mm
Door opening angle	250 degrees
Height adjustment interval	40
Cylinder lock	modular barrel
Type of product	Enclosed trolley

---

## Accessories

Intermediate shelf for slotting into mesh trolley TG9 Platform area depth 700 mm	918578 700
---	------------