

Garant
Thread cutting set with spiral point taps, for metric threads: M3-12

Order data

| | |
|--------------|---------------|
| Order number | 145312 M3-12 |
| GTIN | 4062406301538 |
| Item class | 11K |

Description
Version:

Strong sheet metal case with carrying handle and 2 offset catches. Each tool is securely stored in its own holder and immediately ready to hand. The taps are raised up vertically when the lid is opened. For more detailed descriptions of the content see individual products.

Content:

3 each spiral point tap No. 131450: Size M3; M4; M5; M6; M8; M10; M12
 1 each die No. 140300: Size M3; M4; M5; M6; M8; M10; M12
 1 each jobber drill No. 114150: Size 2.5; 3.3; 4.2; 5; 6.8; 8.5; 10.2
 1 each adjustable tap wrench No. 148410: Size 1; 2
 1 tap wrench with ratchet No. 148700: Size 85
 1 each die stock No. 149310: Size 20×5; 20×7; 25×9; 30×11; 38×14
 1 thread gauge No. 477000: Size M/W
 1 screwdriver No. 664300: Size 3×60

Technical description

| | |
|--------------------|----------|
| for metric threads | M3 – M12 |
| Length | 420 mm |

| | |
|-----------------|------------|
| Height | 55 mm |
| Width | 223 mm |
| Thread type | M |
| Flank angle | 60 degrees |
| Type of product | Die |

Accessories

| | |
|--|--------------|
| Jobber drill HSSN Ø DC h8 (mm or inch) 2,5 | 114150 2,5 |
| Die6g M M8 | 140300 M8 |
| Thread gauge for threads M/W | 477000 M/W |
| Spiral point tapshort M M10 | 131450 M10 |
| Jobber drill HSSN Ø DC h8 (mm or inch) 10,2 | 114150 10,2 |
| Die6g M M5 | 140300 M5 |
| Jobber drill HSSN Ø DC h8 (mm or inch) 4,2 | 114150 4,2 |
| Die6g M M12 | 140300 M12 |
| Die6g M M3 | 140300 M3 |
| Jobber drill HSSN Ø DC h8 (mm or inch) 8,5 | 114150 8,5 |
| Die6g M M6 | 140300 M6 |
| Die stock for die Ø × height 20X7 mm | 149310 20X7 |
| T-tap wrench with ratchet Overall length 85 mm | 148700 85 |
| Die stock for die Ø × height 30X11 mm | 149310 30X11 |
| Spiral point tapshort M M5 | 131450 M5 |
| Jobber drill HSSN Ø DC h8 (mm or inch) 5 | 114150 5 |
| Die stock for die Ø × height 20X5 mm | 149310 20X5 |
| Die6g M M4 | 140300 M4 |
| Tap wrench, adjustable Type 2 | 148410 2 |
| Jobber drill HSSN Ø DC h8 (mm or inch) 3,3 | 114150 3,3 |
| Spiral point tapshort M M4 | 131450 M4 |

| | |
|--|--------------|
| Spiral point tapshort M M12 | 131450 M12 |
| Jobber drill HSSN Ø DC h8 (mm or inch) 6,8 | 114150 6,8 |
| Die6g M M10 | 140300 M10 |
| Die stock for die Ø × height 25X9 mm | 149310 25X9 |
| Tap wrench, adjustable Type 1 | 148410 1 |
| Spiral point tapshort M M8 | 131450 M8 |
| Die stock for die Ø × height 38X14 mm | 149310 38X14 |
| Spiral point tapshort M M6 | 131450 M6 |
| Spiral point tapshort M M3 | 131450 M3 |
| Sheet metal case empty for thread cutting set for metric threads M3-12 | 145605 M3-12 |