

Garant GRIDLINE

## Mobility unit for GridLine cabinets, factory fitted, suitable for casing depth in G: 20



### Order data

Order number	958482 20
GTIN	4062406301118
Item class	9GK

### Description

#### Version:

GridLine mobility unit consisting of 2 galvanized sheet metal cross beams. Completely assembled with set of wheels and 1 set of 2-component Haptoprene® push handle. For bolting on to GridLine cabinets and tool cabinets. **Push the cabinet from the side.**

Factory fitted when GridLine cabinets and mobility unit are ordered at the same time.

#### Suitable for:

Cabinets No. 940001 – 940123; No. 940801 – 940863.

#### Supplied with:

1 × cross beam with 2 castors with parking brakes, 1 × cross beam with 2 fixed wheels, 1 × push handle set.

#### Attention:

**Because of the risk of tipping over, when installing the mobility unit comply strictly with the specified maximum cabinet height.**

**When calculating the load capacity, please take account of the tare weight of the cabinet / tool cabinet.**

#### Note:

Mobility unit suitable for GridLine cabinets up to a maximum height of 1250 mm. Maximum load capacity overall 200 kg. **Only for GridLine cabinets without drawers.**

### Technical description

Castor Ø	125 mm
----------	--------

Fixed wheel Ø	125 mm
Depth	500 mm
maximum load capacity	200 kg
Carriage height	160 mm
Type of product	Wheels and push handle