



Water-tight case "Explorer", Type: 4216



Order data

Order number	692930 4216
GTIN	8024482185040
Item class	64A

Description

Version:

Extremely sturdy tool case of impact resistant plastic, filled with pre-shaped chequer foam. Lockable with padlock No. 085830 – 085875. Thick walls throughout for high stability. Pressure-tight and resistant to chemicals. Temperature-resistant from –33 °C to 90 °C.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

For protection, packaging, and transport of delicate parts and devices.

Note:

Many other case sizes, fittings variants, and accessories available on request.

Technical description

Weight	3.2 kg
Volume	20 l
Internal dimension width	300 mm

Number of catches	2
Internal dimension height	160 mm
maximum loading	22 kg
External dimension width	366 mm
External dimension length	457 mm
External dimension height	183 mm
Internal dimension length	420 mm
IP Index of Protection	IP 67
Characteristics case	impact resistant
Characteristics case	stackable
Characteristics case	suitable for air travel
Type of product	Tool transport system