



## Pneumatic screwdriver, Type: S2308



### Order data

Order number	079163 S2308
GTIN	7322590010027
Item class	03R

### Description

#### Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø.

- **With slip clutch.**
- **Adjustable torque setting.**
- **Reversible for clockwise/ anticlockwise rotation.**

Particularly suitable for series production screwdriving with quick-release bit holder for E 6.3 bits (see No. 674205 ff).

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

### Technical description

maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Torque range	2,5 – 11 Nm
maximum screw Ø (8.8 - 12.9)	M6
recommended hose size (internal Ø)	10 mm
Operating noise	82 dB(A)

Weight	1.1 kg
maximum air consumption	504 l/min
Format	Pistol
Manufacturer's designation	S2308
maximum speed	950 min <sup>-1</sup>
Compressed air connection	1/4 in
Connection thread	BSP
Bit socket	F 6.3
Type of product	Screwdriver