

Garant**Boring bar stabiliser 5×D mini, Type: 20L****Order data**

Order number	319461 20L
GTIN	4062406309282
Item class	31V

Description**Version:**

Base body of high-quality tool steel, surface and functional faces hardened.

Advantage:

Reduces oscillation and vibration when used with all types of boring bars.

Suitable for:

All popular boring bars.

Note:

To determine the right type of boring bar stabiliser, it is essential to perform a collision check using the Hoffmann e-Tool data from the eShop or via the ToolScout! We recommend a maximum overhang length of 3×D of the types of boring bar used.

Maximum overhang, stabiliser incl. boring bar 8×D.

Boring bar stabiliser with 7×D or shank Ø D₂ = 25 mm available on request.

Technical description

Shank length L _s	60 mm
Overhang L ₁	100 mm
Clamping Ø D ₁	20 mm
Shank Ø D ₂	32 mm
Overall length L ₂	166 mm
Offset Z to the axis	15 mm
Radius R	1.2 mm

C	1 mm
Ø D ₃	40 mm
Cutting direction	left-hand
Boring depth up to	5×D
Vibration	damped
Type of product	Boring bar stabiliser