



## Pneumatic screwdriver, Type: S2310



### Order data

Order number	079163 S2310
GTIN	7322590036980
Item class	03R

### Description

#### Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø.

- **With slip clutch.**
- **Adjustable torque setting.**
- **Reversible for clockwise/ anticlockwise rotation.**

Particularly suitable for series production screwdriving with quick-release bit holder for E 6.3 bits (see No. 674205 ff).

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Torque range: 2 – 15 N·m

maximum screw Ø (8.8 - 12.9): M8

maximum speed: 800 min<sup>-1</sup>

Bit socket: F 6.3

Format: Pistol

maximum air consumption: 510 l/min

### Technical description

Operating noise	81 dB(A)
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Torque range	2 – 15 N·m
Weight	1.4 kg
maximum air consumption	510 l/min
recommended hose size (internal Ø)	10 mm
maximum screw Ø (8.8 - 12.9)	M8
Format	Pistol
maximum speed	800 min <sup>-1</sup>
Manufacturer's designation	S2310
Compressed air connection	1/4 in
Connection thread	BSP
Bit socket	F 6.3
Type of product	Screwdriver