



Pneumatic ratchet screwdriver, Type: W2611



Order data

Order number	079121 W2611
GTIN	7322590034122
Item class	03R

Description

Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal \emptyset . Reversible ratchet screwdriver with speed control in a compact design with glass-fibre composite casing for good thermal insulation. Exhaust air outlet can be rotated 360°. Overall length only 192 mm, ideal for restricted spaces.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

maximum speed	280 min ⁻¹
maximum screw \emptyset (8.8 - 12.9)	M8
Manufacturer's designation	W2611
Operating noise	85 dB(A)
Weight	0.5 kg
recommended hose size (internal \emptyset)	10 mm

Tool arbor size	1/4 in
Torque range	4 - 40 Nm
Length	192 mm
maximum vibration to EN	8,8 m/s ²
maximum air consumption	540 l/min
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Screwdriver