

## Garant

### Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC m6 (mm or inch): 6,1



#### Order data

Order number	123008 6,1
GTIN	4045197569509
Item class	11E

#### Description

##### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. High roundness and alignment accuracy of the deep hole, thanks to **4 guide chamfers**. Outstanding chip evacuation due to **4 internal cooling channels** from Ø 3.8 mm. Up to 3.7 mm Ø with 2 internal cooling channels. **Straight major cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

##### Note:

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 123010**.

Form **HE**: order with **No. 123008 + 129100HE**.

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Standard: Manufacturer's standard

Tolerance nominal Ø: m6

Number of cutting edges Z: 2

recommended maximum drilling depth  $L_2$ : 66.9 mm

Tolerance nominal Ø: m6

Overall length L: 114 mm

Shank Ø  $D_s$ : 8 mm

Feed f in stainless steel > 900 N/mm<sup>2</sup>: 0.12 mm/rev.

#### Technical description

Flute length $L_c$	76 mm
Nominal Ø $D_c$	6.1 mm
Feed f in stainless steel > 900 N/mm <sup>2</sup>	0.12 mm/rev.

Shank tolerance	h6
Number of cutting edges Z	2
Tolerance nominal $\varnothing$	m6
Shank $\varnothing D_s$	8 mm
Overall length L	114 mm
Standard	Manufacturer's standard
recommended maximum drilling depth $L_2$	66.9 mm
Coating	TiAlN
Tool material	Solid carbide
Version	8xD
Point angle	140°
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	blue
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	75 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	55 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	32 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	70 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	60 m/min	M
wet maximum	suitable		
wet minimum	suitable		

## Services

Shank grinding Type HE

129100 HE