



Pneumatic ratchet screwdriver, Type: W2621



Order data

Order number	079121 W2621
GTIN	7322590034146
Item class	03R

Description

Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal \emptyset . Reversible ratchet screwdriver with speed control in a compact design with glass-fibre composite casing for good thermal insulation. Exhaust air outlet can be rotated 360°.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

Tool arbor size	3/8 in
Weight	1.1 kg
recommended hose size (internal \emptyset)	10 mm
maximum speed	170 min ⁻¹
Length	271 mm
Operating noise	87 dB(A)
maximum screw \emptyset (8.8 - 12.9)	M12
Torque range	5 - 68 Nm

maximum air consumption	600 l/min
maximum vibration to EN	15 m/s ²
Manufacturer's designation	W2621
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Screwdriver