

Garant
Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlN, Ø DC m6: 8,2 mm

Order data

Order number	122432 8,2
GTIN	4045197539786
Item class	11E

Description
Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. Excellent chip evacuation due to **4 internal coolant channels**. **Straight cutting edges** with honed edges and special flute profile for **short chips**. **Special coating** for the **best tool life** and **high metal removal rates**.

Recommendation:
Maximum drilling depth:

Flute length (see table) less 1.5×nominal Ø.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$ -

Machining strategy: HPC

Standard: DIN 6537 K

Tolerance nominal Ø: m6

Number of cutting edges Z: 2

Semi-Standard: yes

Tolerance nominal Ø: m6

recommended maximum drilling depth L_2 : 34.7 mm

Overall length L: 89 mm

Shank Ø D_s : 10 mm

Feed f in Inconel®: 0.12 mm/rev.

Technical description

Feed f in Inconel®	0.12 mm/rev.
Number of cutting edges Z	2
Flute length L_c	47 mm

Shank tolerance	h6
Nominal $\varnothing D_c$	8.2 mm
Tolerance nominal \varnothing	m6
Shank $\varnothing D_s$	10 mm
Overall length L	89 mm
Standard	DIN 6537 K
recommended maximum drilling depth L_2	34.7 mm
Semi-Standard	yes
Coating	TiAlN
Tool material	Solid carbide
Drill depth up to	4xD
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Colour ring	pink
Type of product	Jobber drill