



Pneumatic power drill, Type: D2112Q



Order data

Order number	079051 D2112Q
GTIN	7322590019778
Item class	03R

Description

Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø. A range of powerful and very smooth running drills with pistol grip and a drilling power of up to 13 mm in steel. Exhaust air is discharged through the handle, to prevent drill chips from swirling up. With quick-release chuck.

Function:

IP20: No protection against penetration by foreign bodies with Ø < 12 mm, however touching should be avoided, and no protection against water.

Supplied with:

Quick-clamping chuck.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Output power: 350 W

maximum speed: 0 - 5400 min⁻¹

Quick-clamping chuck range: 1.5 - 10 mm

maximum air consumption: 600 l/min

Connection thread: BSP

Compressed air connection: 1/4 in

Technical description

maximum vibration to EN	< 2.5 m/s ²
maximum speed	0 - 5400 min ⁻¹
Length	211 mm
Weight	1 kg
Output power	350 W
Quick-clamping chuck range	1.5 - 10 mm
Manufacturer's designation	D2112Q
maximum air consumption	600 l/min
Operating noise	80 dB(A)
recommended hose size (internal Ø)	10 mm
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Drill