



## Pneumatic drill, Type: D2112Q



### Order data

Order number	079051 D2112Q
GTIN	7322590019778
Item class	03R

### Description

#### Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø. A range of powerful and very smooth running drills with pistol grip and a drilling power of up to 13 mm in steel. Exhaust air is discharged through the handle, to prevent drill chips from swirling up. With quick-release chuck.

#### Supplied with:

**Quick-clamping chuck.**

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

### Technical description

maximum vibration to EN	< 2.5 m/s <sup>2</sup>
maximum speed	0 - 5400 min <sup>-1</sup>
Length	211 mm
Weight	1 kg
Output power	350 W
Quick-clamping chuck range	1.5 - 10 mm

Manufacturer's designation	D2112Q
maximum air consumption	600 l/min
Operating noise	80 dB(A)
recommended hose size (internal Ø)	10 mm
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Drill