



## Solid carbide high performance drill, Whistle-Notch shank DIN 6535 HE, TiN, Ø DC h7: 8,7mm



### Order data

Order number	122320 8,7
GTIN	4045197390554
Item class	12E

### Description

#### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**NEW GENERATION AVAILABLE!**

**Recommended successor product is No. 122503.**

### Technical description

Number of cutting edges Z	2
Shank tolerance	h6
Feed f in steel < 900 N/mm <sup>2</sup>	0.18 mm/rev.
Nominal Ø D <sub>c</sub>	8.7 mm
Flute length L <sub>c</sub>	47 mm
Tolerance nominal Ø	h7
Shank Ø D <sub>s</sub>	10 mm
Overall length L	89 mm
Standard	DIN 6537 K
recommended maximum drilling depth L <sub>2</sub>	34 mm

Coating	TiN
Tool material	Solid carbide
Version	4xD
Point angle	140 degrees
Shank	DIN 6535 HE to h6
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	75 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	65 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	P
GG(G)	suitable only under restricted conditions	70 m/min	K
wet maximum	suitable		
dry	suitable		