

**Pneumatic shut-off screwdriver, Type: S2428L****Order data**

Order number	079165 S2428L
GTIN	
Item class	03R

Description**Version:**

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø.

- **Precise, non-wearing cut-out clutch.**
- **High torque accuracy.**

Particularly suitable for series production screwdriving with quick-release bit holder for E 6.3 bits (see No. 674200 ff).

Oil-free - no additional pneumatic oiler required. With Push-Start, rotation starts on contact with the screw connection.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

Tool arbor size	1/4 in
Manufacturer's designation	S2428L
maximum screw Ø (8.8 - 12.9)	M5
recommended hose size (internal Ø)	10 mm
maximum speed	700 min ⁻¹
Torque range	3.5 - 7 Nm

Operating noise	70 dB(A)
maximum air consumption	360 l/min
Format	Rod
maximum vibration to EN	$< 2.5 \text{ m/s}^2$
Weight	1 kg
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Screwdriver