

HOLEX
Solid carbide high performance drill, plain shank DIN 6535 HA, TiN, Ø DC h7 (mm or inch): 1,8

Order data

Order number	122340 1,8
GTIN	4045197262257
Item class	12E

Description
Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

NEW GENERATION AVAILABLE!

Recommended successor product is No. 122504.

Versions with HB and HE shank available at the same price as HA.

HB shank: use order **No. 122345**.

HE shank: use order **No. 122355**.

Technical description

Feed f in steel < 900 N/mm ²	0.06 mm/rev.
Nominal Ø D _c	1.8 mm
Shank tolerance	h6
Number of cutting edges Z	2
Flute length L _c	14 mm
Tolerance nominal Ø	h7
Shank Ø D _s	4 mm
Overall length L	55 mm

Standard	DIN 6537 K
recommended maximum drilling depth L ₂	11.3 mm
Coating	TiN
Tool material	Solid carbide
Version	4×D
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	240 m/min	N
Steel < 500 N/mm ²	suitable	110 m/min	P
Steel < 750 N/mm ²	suitable	90 m/min	P
Steel < 900 N/mm ²	suitable	80 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	65 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	35 m/min	P
INOX < 900 N/mm ²	suitable	35 m/min	M
INOX > 900 N/mm ²	suitable	30 m/min	M
Ti > 850 N/mm ²	suitable	30 m/min	S
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		

Air

suitable only under
restricted conditions