



## Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø h7: 17,3 mm

### Order data

Order number	122440 17,3
GTIN	4045197048875
Item class	11E

### Description

#### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry. Convex cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

#### Recommendation:

##### Maximum drilling depth:

clamping slot length (see table) less 1.5×nominal Ø.

#### Note:

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122445/122505**.

Form **HE**: order with **No. 122440/122500** and **129100HE**.

#### **NEW GENERATION AVAILABLE!**

**Recommended successor products are No. 122415; 122425 and 122435.**

Tool material: Solid carbide

Drill depth up to: 4×D

Point angle: 140 degrees

Schaft: DIN 6535 HA to h6

Through-coolant: false

Machining strategy: HPC

Norm: DIN 6537 K

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

Tolerance nominal Ø: h7

Flute length: 73 mm

Overall length  $L_{tot}$ : 123 mm

Shank Ø: 18 mm

Feed  $f$  in steel < 1100 N/mm<sup>2</sup>: 0.35 mm/rev.

### Technical description

Point angle	140 degrees
Tool material	Solid carbide
Type	
Machining strategy	HPC
Through-coolant	no
Colour ring	green
Use for drilling	
Pilot drill required	
Drill depth up to	4×D
Cutting direction	
Hole tolerance	
Coating	TiAlN
Helix angle	degrees
Schaft	DIN 6535 HA to h6
Series	
Type of product	