

Garant
Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 6,2mm

Order data

| | |
|--------------|---------------|
| Order number | 122445 6,2 |
| GTIN | 4045197389916 |
| Item class | 11E |

Description
Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Convex cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

NEW GENERATION AVAILABLE!

Recommended successor product is No. 122416.

Technical description

| | |
|--|-------------|
| Shank tolerance | h6 |
| Number of cutting edges Z | 2 |
| Flute length L_c | 34 mm |
| Feed f in steel < 1100 N/mm ² | 0.2 mm/rev. |
| Nominal Ø D_c | 6.2 mm |
| Tolerance nominal Ø | h7 |
| Shank Ø D_s | 8 mm |
| Overall length L | 79 mm |
| Standard | DIN 6537 K |
| recommended maximum drilling depth L_2 | 24.7 mm |
| Coating | TiAlN |

| | |
|--------------------|-------------------|
| Tool material | Solid carbide |
| Version | 4×D |
| Point angle | 140 degrees |
| Shank | DIN 6535 HB to h6 |
| Through-coolant | no |
| Machining strategy | HPC |
| Colour ring | green |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 500 N/mm ² | suitable only under restricted conditions | 90 m/min | P |
| Steel < 750 N/mm ² | suitable | 80 m/min | P |
| Steel < 900 N/mm ² | suitable | 70 m/min | P |
| Steel < 1100 N/mm ² | suitable | 65 m/min | P |
| Steel < 1400 N/mm ² | suitable | 35 m/min | P |
| Ti > 850 N/mm ² | suitable only under restricted conditions | 35 m/min | S |
| GG(G) | suitable | 70 m/min | K |
| Uni | suitable | | |
| wet maximum | suitable | | |
| dry | suitable | | |