

**Garant**
**Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 15mm**

**Order data**

Order number	122445 15
GTIN	4045197390783
Item class	11E

**Description**
**Version:**

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Convex cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**NEW GENERATION AVAILABLE!**

**Recommended successor product is No. 122416.**

**Technical description**

Shank tolerance	h6
Nominal Ø D <sub>c</sub>	15 mm
Number of cutting edges Z	2
Feed f in steel < 1100 N/mm <sup>2</sup>	0.32 mm/rev.
Flute length L <sub>c</sub>	65 mm
Tolerance nominal Ø	h7
Shank Ø D <sub>s</sub>	16 mm
Overall length L	115 mm
Standard	DIN 6537 K
recommended maximum drilling depth L <sub>2</sub>	42.5 mm
Coating	TiAlN

Tool material	Solid carbide
Version	4×D
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable only under restricted conditions	90 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	65 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	35 m/min	P
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	S
GG(G)	suitable	70 m/min	K
Uni	suitable		
wet maximum	suitable		
dry	suitable		