



## Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlN, Ø h7: 9,1 mm



### Order data

Order number	123102 9,1
GTIN	4045197458674
Item class	11E

### Description

#### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**.

Particularly high alignment accuracy due to **4 guide chamfers** which stabilise the drill even at extreme depths!

**Convex cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

#### Advantage:

**High process reliability and surface quality of the hole.**

#### Recommendation:

##### Maximum drilling depth:

clamping slot length (see table) less 1.5×nominal Ø.

#### Note:

**NEW GENERATION AVAILABLE!**

**Recommended successor products are No. 123026 and 123036.**

Machining strategy: HPC

Norm: Manufacturer's standard

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

Tolerance nominal Ø: h7

Flute length: 95 mm

Overall length  $L_{tot}$ : 142 mm

Shank Ø: 10 mm

Feed  $f$  in steel < 1100 N/mm<sup>2</sup>: 0.2 mm/rev.

### Technical description

Nominal Ø	9.1 mm
-----------	--------

Shank tolerance	h6
Feed f in steel < 1100 N/mm <sup>2</sup>	0.2 mm/rev.
Number of cutting edges Z	2
Flute length	95 mm
Tolerance nominal Ø	h7
Shank Ø	10 mm
Overall length L <sub>tot</sub>	142 mm
Norm	Manufacturer's standard
recommended maximum drilling depth	81.4 mm
Coating	TiAlN
Tool material	Solid carbide
Drill depth up to	8×D
Point angle	135 degrees
Skaft	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Colour ring	green